Specifications





Photo is representative



Eaton STN061050BL40

Eaton TVS diode ESD supp. DFN0603-2L size, 5 op. voltage, 0.4 pF, 18 kV, Bidirectional

General specifications

PRODUCT NAME	Eaton TVS diode ESD suppressor
CATALOG NUMBER	STN061050BL40
UPC	051712771856
PRODUCT LENGTH/DEPTH	0.65 mm
PRODUCT HEIGHT	0.32 mm
PRODUCT WIDTH	0.35 mm
PRODUCT WEIGHT	0.00028 g
COMPLIANCES	RoHS Compliant
PRODUCT TYPE	ESD suppressor

Powering Business Worldwide

Downloaded from Arrow.com.

Voltage, current and power ratings

VOLTAGE RATING	5 V
CLAMPING VOLTAGE	20

Package size, operating temperature, ESD rating

CAPACITANCE	0.4
ESD WITHSTAND - AIR	18
ESD WITHSTAND - CONTACT	18
OPERATING TEMPERATURE - MIN	-55 °C
OPERATING TEMPERATURE - MAX	125 °C

Resources

SPECIFICATIONS AND DATASHEETS	Eaton stn061050bl40 TVS diode ESD suppressor data sheet Eaton Specification Sheet - STN061050BL40

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

Downloaded from Arrow.com.