

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2451351020

Status:


Active

Overview:

Mini-Fit Jr. Power Connectors

Description:

Mini-Fit Jr.-to-Mini-Fit Jr. Off-the-Shelf (OTS) Overmolded Cable Assembly, Dual Row, 2.0m Length, 10 Circuits, Black



Documents:	
3D Model	Packaging Specification 2027040002-PK (PDF)
Drawing (PDF)	Datasheet (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	Cable Assemblies
Series	245135
Application	Power, Wire-to-Board, Wire-to-Wire
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Mini-Fit Jr. Both Ends
Overmolded	Yes
Overview	Mini-Fit Jr. Power Connectors
Product Name	Mini-Fit Jr.
Type	Overmolded Assembly
UPC	889056878173
Physical	
Cable Length	2.0m
Circuits (Loaded)	10
Color - Resin	Black
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	319.000/g
Number of Rows	2
Packaging Type	Bag
Pitch - Mating Interface	4.20mm
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	5.40mm
Wire Size AWG	18
Wire/Cable Type	UL 2464
Electrical	
Current - Maximum per Contact	8.4A
Voltage - Maximum	300V AC
Material Info	
Reference - Drawing Numbers	
Packaging Specification	2027040002-PK
Sales Drawing	2014400066-000

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)4578-DC (25
June 2020)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Compliant

Not Contained

Search Parts in this Series
245135 Series

Mates With
Dual Row Plug Housing [5559](#)
Dual Row Header [5566](#) , [5569](#) , [87427](#)
Dual Row BMI Header [43810](#) , [44068](#) , [42404](#) , [42440](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION