
MICRO SWITCH
FREEPORT, ILLINOIS, U.S.A.
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929

SWITCH-BASIC

CATALOG LISTING
BZ-3YQ18T



NOTES
1. MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .139 MAX DIA ON 1.000±.002 CENTERS
2. SWITCH WILL PERFORM SATISFACTORILY IN TEMPERATURES TO MINUS 65° F
3. HARDWARE FURNISHED UNASSEMBLED

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

OPERATING FORCE	16-26 OZ
RELEASE FORCE	4 OZ MIN
DIFFERENTIAL TRAVEL	.001-.004
OVERTRAVEL	.140 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
SINGLE POLE DOUBLE THROW SPLIT CONTACT

UNDERWRITERS' LAB. INC. LISTED RATING
-L4- 5 A-250 VAC

SCALE FULL
DO NOT SCALE PRINT

UNLESS OTHERWISE NOTED DIMENSIONS ARE IN INCHES
TOLERANCES ARE:

ONE PLACE	(.0)	±.030
TWO PLACE	(.00)	±.015
THREE PLACE	(.000)	±.005
ANGLES		±

WEIGHT .088 LB

BZ-3YQ18T | M | DRAWING NUMBER | ISSUE 8 | RELEASE NO. SR12586 | REPLACES

REVISIONS

A	SR12586	M B F 1 DEC 66	
B	CO-69351-D	JWB 18 JUL 91	6 NOV '63
C	CO-77590	SAR 11 JUN 94	BRJ
D	CO-77462-B	DLT 30 JUN 94	CHECK
E	CO-82133	CSL 1 AUG 96	
F	0005508	PEH/AP 18 MAY 04	6 NOV '63
G	0005642	TCC/AP 26 MAY 04	DAW

CHECK | 5 OCT 63 | DRAWN M B F | FORMTEK FO-50378

Downloaded from Arrow.com.