

Heavy Duty Steel Instrument 1453 Series

Key Features:



- All steel, heavy duty construction designed to house heavy, heat producing items such as power supplies.
- Bottom of unit is 16 gauge steel, top is 18 gauge steel.
- Finished in a rugged beige powder coat.
- Top half is of an upside down "U" shape design for easy removal, bottom half is also "U" shaped but includes a fold on all sides including front & back for extra strength and mounting of top case.
- Top case section is heavily ventilated for excellent air circulation with an attractive slant (also doubles as a lifting area - both front & back).
- Top lip extends 0.75" (19 mm) on both sides adding 1.5" (38 mm) to the total depth.
- Bottom is solid except for 4 holes for mounting heavy duty rubber feet.
- Includes nickel plated self-tapping screws and screw on 0.75" (19 mm) high, rubber feet (**1421T7**).

Enclosures

Part Number	Height	Width	Depth
1453B	6.00	6.00	9.50
1453C	7.00	7.00	11.00
1453K	10.00	9.00	18.00
1453N	12.00	12.00	19.00

Tags: instrument, steel instrument, steel enclosure, vented

Data subject to change without notice.

© 2026. Hammond Manufacturing Ltd. All rights reserved.