

Part Number : [1300000052](#)

Product Description : Quick-Change Single-Ended Cordset, 3 Poles, Female (Straight) to Pigtail, 12 AWG, Yellow CPE Cable, 3.66m (12.0') Length

Series Number : 130000

Status : Active

Product Category : Circular Industrial Cordsets

Engineering Part Number : 32356



Documents and Resources

Drawings

[1300000052 sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Compliant with Exemption 3 per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Not Reviewed per D(2025)6375-DC (05 Nov 2025) SCIP:4a4c481d-0f25-430c-950b-832fd50a1323
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	130000
Description	Quick-Change Single-Ended Cordset, 3 Poles, Female (Straight) to Pigtail, 12 AWG, Yellow CPE Cable, 3.66m (12.0') Length
IP Rating	IP67
Product Name	Quick-Change
Type	Single Ended
UPC	78678832356

Agency

CSA	LR6837
UL	E46237

Electrical

Current - Maximum per Contact	25.0A
Voltage - Maximum	600V

Physical

Cable Diameter	16.63mm (.655")
Cable Length	3.66m (12.0')
Color - Cable Jacket	Yellow
Connector End A	Quick-Change
Connector End B	Pigtail

Coupling Style	Threaded
Gender	Female-Pigtail
Keyway	Single
LED Indicator	None
Material - Cable Jacket	CPE
Material - Connector Body	TPE
Material - Contact	Copper Alloy
Material - Coupling Nut	Nylon
Material - Plating Mating	N/A
Net Weight	584.000/g
Orientation	Straight to Pigtail
Poles	3
Temperature Range - Operating	-20° to +105°C
Wire/Cable Type	SOW
Wire Size (AWG)	12

This document was generated on Dec 29, 2025