



Overview

Lead time	Usually in Stock
-----------	------------------

General

Provided equipment	User manual Rack mounting brackets
--------------------	---------------------------------------

Physical

Colour	Black
Depth	13.2 cm
Height	3.7 cm
Product weight	1.18 kg
Number of rack unit	1U
Width	25 cm

Input

Input voltage	100 V 120 V 200 V 208 V 230 V
Plug standard	IEC 60320 C14

Conformance

Product certifications	cUL listed CE TÜV UL listed
Standards	EN 60950 FCC part 15 class A

Environmental

Ambient air temperature for operation	0...45 °C
---------------------------------------	-----------

Relative humidity	10...90 %
Ambient air temperature for storage	-15...65 °C
Storage Relative Humidity	10...90 %

Packing Units

Package 1 Weight	2 kg
Package 1 Height	10.2 cm
Package 1 width	52.1 cm
Package 1 Length	21.3 cm

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------