




Rev	AWO #	Description	Date	Appr
-		RELEASED	4/12/05	

APPROVED: _____
DATE: _____ TITLE: _____



Positions: 2 thru 20
A = .156 [3.96] x No. of Positions + .016 [0.40]
B = .156 [3.96] x No. of Spaces

SPECIFICATIONS:
Material:
Insulator: Nylon 66, rated UL 94V-2
Insulator color: White
Electrical:
Operating voltage: 250 VAC max
Current rating: 5 Amps max
Insulation resistance: 1,000 Mohms min
Dielectric withstanding voltage: 1,500 VAC for 1 minute
Temperature Rating:
Operating temperature: -25°C to +85°C
Environmental:
Lead free, RoHS compliant

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]		ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
TOLERANCES: EXCEPT AS NOTED	HOLES		
.X ± .10	ØXX ± .10		
.XX ± .020	ØXXX ± .015		
.XXX ± .015	ØXXX ± .010	ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
APPROVALS	DATE		
DRAWN SS	4/12/05		
CHECKED			
APPROVED		ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

.156 [3.96] WIRE HOUSING

TITLE	SIZE	PART NO.	REV.
	X	MTB-XX	-
REF:		SCALE: NTS	SHEET 1 OF 1

