



+ APPLICATION TOOLING
HAND TOOLS



✓ Active

TE CONNECTIVITY (TE)
MATRIZE .250 FF
AMP

539654-2
TE Internal Number: 539654-2

Out of Scope for EU RoHS
Out of Scope for EU ELV

Tool Grade Commercial Crimp Tooling
Ratchet Configuration Operator Releasable & Adjustable
Die Sets Type Removable/Interchangeable
Specification Type TE Product Specification (114-)
Calibration Certificate No

↓ **PRODUCT DRAWING**
English

DOCUMENTATION

Product Drawings

ERGOCRIMP Die Set For 6.3 Mm FASTIN-FASTON
PDF (TIFF AVAILABLE)
English

Instruction Sheets

Instruction Sheet (non U.S.)

Instruction Sheet ERGOCRIMP Die P/N 539654-2
PDF
German

FEATURES

Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Other

- Tool Grade** Commercial Crimp Tooling
- Ratchet Configuration** Operator Releasable & Adjustable
- Die Sets Type** Removable/Interchangeable
- Specification Type** TE Product Specification (114-)
- Calibration Certificate** No
- Power Type** Manual
- Tool Type** Ergocrimp Hand Tool Assembly or Die
- Crimp Form-Wire Barrel Type** Open Barrel - F Crimp

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance
PDF