Part Number : 733862360
Product Description : Precision Test Adapter, Between-Series, 2.4mm Jack-to-2.92mm Jack, Straight, Passivated, 40 GHz, 50 Ohms
Series Number : 73386
Status : Active
Product Category : RF / Coaxial Connectors



Documents and Resources

Drawings

733862360_sd.pdf

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Downloaded from Arrow.com.

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73386
Description	Precision Test Adapter, Between-Series, 2.4mm Jack-to-2.92mm Jack, Straight, Passivated, 40 GHz, 50 Ohms
Application	RF
Product Name	Precision Test - 2.4mm,Precision Test - 2.92mm
Style	Adapter, Between-Series Adapter
Type	Subminiature
UPC	196823316982

Electrical

Frequency	40 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 335 Vrms@Sea Level

Physical

Cable Attachment	N/A
Gender	Jack/Jack
Keying to Mating Part	N/A
Net Weight	3.265/g
Orientation	Straight
Packaging Type	Bag
Panel Mount	No
Panel Mount Method	N/A
PCB Mounting	N/A
PCB Thickness - Recommended	N/A
Reverse Polar	No
Wire/Cable Type	N/A

Downloaded from Arrow.com.

Downloaded from Arrow.com.