



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF AMPHENOL CABLES ON DEMAND. ANY REPRODUCTION OR DISCLOSURE TO THIRD PARTIES IN PART OR WHOLE, WITHOUT THE EXPRESS WRITTEN PERMISSION OF AMPHENOL CABLES ON DEMAND IS PROHIBITED.

REV.	DESCRIPTION	REVISIONS	DATE	APPROVED
A	NEW RELEASE		1/15/2009	
A1	ADD 1.5" FT		22/OCT/09	
A2	ADD 1.4" INCH		20/MAY/10	
A3	ADD 1.5" FT 14 FT 16 FT		8/OCT/15	
A4	ADD 1.4" 10mm		13/Sep/2017	
A5	ADD 1.5" & 20" & 25" & 30"		6/Jun/2018	



SECTION A-A

- NOTES:
1. CABLE: 126AWG(7/0, .16±0.008mm)*1C +BRAID(.16*4/0, .12±0.008mm) TINNED COPPER INSULATION: PE OD= 1.52±0.07mm ; COLOR: TRANSPARENT JACKET: HALF MATTE PVC LOW TOXIC; OD= Ø2.54±0.10mm COLOR: UL813 BLACK.
 - MARKING: RG-174/U COAXIAL CABLE RoHS
 2. CONNECTOR: SMA Male GOLD-PLATING
 3. OPEN/SHORT MISS WIRE TEST 100%
 4. CONDUCTOR RESISTANCE ≤ 150Ω/km
 5. INSULATION RESISTANCE ≥ 2MΩ DC300V 0.01Sec
- ALL MATERIALS SHALL ACCORD WITH RoHS STANDARD.

PIN OUT:

CENTER	CENTER
SHELL	SHELL

LENGTH	P/N
6 INCH(152±15mm)	CO-174SMAAX200-000.6
8 INCH(203±15mm)	CO-174SMAAX200-000.8
10 INCH(254±15mm)	CO-174SMAAX200-000.10
410MM(410±20mm)	CO-174SMAAX200-410MM
1FT(305±20mm)	CO-174SMAAX200-001
2FT(610±30mm)	CO-174SMAAX200-002
3FT(914±30mm)	CO-174SMAAX200-003
4FT(1219±30mm)	CO-174SMAAX200-004
5FT(1524±30mm)	CO-174SMAAX200-005
7FT(2134±40mm)	CO-174SMAAX200-007
7.5FT(2286±40mm)	CO-174SMAAX200-007.5
10FT(3048±40mm)	CO-174SMAAX200-010
12FT(3658±50mm)	CO-174SMAAX200-012
14FT(4267±50mm)	CO-174SMAAX200-014
15FT(4572±50mm)	CO-174SMAAX200-015
16FT(4877±50mm)	CO-174SMAAX200-016
20FT(6096±75mm)	CO-174SMAAX200-020
25FT(4877±100mm)	CO-174SMAAX200-025
30FT(4877±100mm)	CO-174SMAAX200-030



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE:		E&R NO.	
DECIMALS	ANGLES	APPROVALS	
X	±X	DRAWN	DATE
XX	±XX	LF	8/OCT/15
XXX	±XXX	CHECKED	BA
THIRD ANGLE PROJECTION		RESP ENG	
CDD FILE		SIZE	REV.
		A	A5
20 VALLEY ST. ENDICOTT, NY 13760		CO-174SMAAX200-XXX	
Amphenol Cables on Demand		RG174/U SMA Male / SMA Male	
NOTES: UNLESS OTHERWISE SPECIFIED		SCALE SHEET OF	