



Part Number : [1300180207](#)
Product Description : Mini-Change 4 Pole 90° Adapter, Female to Male
Series Number : 130018
Status : Active
Product Category : Industrial Tees and Splitters
Engineering Number : 41212



Documents & Resources

Drawings
[1300180207_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Not Reviewed per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Part Details

General

Status	Active
Category	Industrial Tees and Splitters
Series	130018
Description	Mini-Change 4 Pole 90° Adapter, Female to Male
IP Rating	IP67
Product Name	Mini-Change
Type	Drop Tee
UPC	78678841212

Agency

CSA	LR6837
UL	E152210

Electrical

Current - Maximum per Contact	8.0A
Voltage - Maximum	600V AC/DC

Physical

Color - Cable Jacket	Yellow
Drop Connector	Mini-Change
Drop Gender	Male
Keyway	Single
LED Indicator	None
Left Trunk Connector	Mini-Change
Left Trunk Gender	Female
Leg 1 Length	N/A
Leg 2 Length	N/A
Length	0.066m
Material - Cable Jacket	N/A
Material - Connector Body	PVC

Material - Coupling Nut	Zinc Die-Cast
Poles	4
Right Trunk Connector	N/A
Right Trunk Gender	N/A
Temperature Range - Operating	-20°C to +80°C

This document was generated on Apr 20, 2025