

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301060118

Status:

Active

Overview:

Description:

Super-Safeway Molded Rubber Stringlight 200W 12/3 SOOW 1.52m (5.0') Lead 5 Sockets with Guards, NEMA L5-20, Overall Length 15.24m (50.0')

Agency Certification	
CSA	LR85374
General	
Product Family	Portable Lighting
Series	130106
NEMA Configuration	NEMA L5-20
NEMA Rating	Rain Tight
Outlet	None
Overview	stringlights
Product Name	Super-Safeway
Type	String Lights
UPC	78678879899
Physical	
Cord Length - Primary	1.52m (5.0')
Cord Length - Secondary	1.52m (5.0')
Depth	47.625mm (1.875")
Duty	Industrial
Guard Included	Yes
Guard Type	Steel
Height	107.95mm (4.250")
Length	15.24m (50.0')
Material - Guard	#8 Gauge Zinc-plated Steel
Mounting Style	Stringer
Packaging Type	Carton
Socket Construction	Rubber Molded
Electrical	
Bulb Type	Incandescent
Cord Type - Primary	12/3 SOOW
Lamp Type	A21
Lamp Wattage - Maximum	200W
Lumens	2000
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ
Material Info	
Engineering Number	323535

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

130106 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION