


Description:	BNC 3-Piece Crimp Plug, 50 Ohm, RG174,188, 316
Part No:	CPM8819
Application:	For Cable RG174, 188, 316
Crimp Tool:	24-9912P
Impedance:	50 Ohms
Fequency Range:	0-4 GHz
Material:	Body Zinc Nickel Plated
	Contact Brass Gold Plated
	Insulator Pom
	Crimp Sleeve Brass Nickel Plated
	Coupling Nut Zinc Nickel Plated
RoHS Compliance:	Yes
Technical Detail:	Refer to Emerson Document P/N 27-0000

DRAWING NO.
CPM8819-CUST

REVISIONS

01	OFFICAL RELEASE	03-05-09 ZG BY T
02	FIGURE OF CONTACT AND CRIMP SLEEVE ARE DIFFERENT WITH BEFORE; BODY MATERIAL: WAS: BRASS; IS: ZINC. INSULATOR MATERIAL: WAS: TEFLON; IS: POM.	03-04-11 JJ JJ D ECO-11-0034



DIM OUTLINE

CUSTOMER COPY

TOLERANCE UNLESS OTHERWISE SPECIFIED		DRAWN BY JEAN.JIN	DATE 03-04-11
DECIMALS	mm	CHECKED BY	DATE
X	± 0.5	JEAN.JIN	03-04-11
X.X	±0.15	APPROVED BY	DATE
X.XX	± 0.1	DONALD	03-04-11
ANGLES	± 0.5°	U/M mm	

THIS DRAWING WAS PRODUCED BY COMPUTER, DO NOT SCALE DRAWING OR UPDATE MANUALLY.

EMERSON Network Power — Connectivity Solutions

TITLE
BNC 3-Piece Crimp Plug, 50 Ohm, RG174,188, 316

SHEET	DRAWING NO.	SIZE
1 OF 1	CPM8819-CUST	A

SOLID EDGE RESELLER COPY

Downloaded from Arrow.com.