
Part Number : 191190007
Product Description : InsulKrimp Long Barrel Flanged Spade Terminal for 22-14 AWG Wire, Stud Size 8 (M4), Length 21.23mm, Carton
Series Number : 19119
Status : Active
Product Category : Ring and Spade Terminals
Engineering Part Number : A-215-08X



Documents and Resources

Drawings

191190007_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

PS-19902-009-001.pdf

PS-19902-013-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

Downloaded from Arrow.com.

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19119
Description	InsulKrimp Long Barrel Flanged Spade Terminal for 22-14 AWG Wire, Stud Size 8 (M4), Length 21.23mm, Carton
Keyword	Spade Terminal, Spade Terminals
Product Name	InsulKrimp
Style	Spade
Type	Spade Connector, Metric Spade Connector
UPC	800753094123

Agency

UL	E32244

Physical

Barrel Type	Open
Color - Resin	Red
Flammability	94V-0

Downloaded from Arrow.com.

Insulation	PVC
Material - Plating Mating	Tin
Net Weight	0.775/g
Packaging Type	Carton
Stud Size	8 (M4)
Wire Insulation Diameter	3.68mm
Wire Size (AWG)	14, 16, 18, 22
Wire Size mm^2	0.25-1.50

Application Tooling

Global

Description	Part Number
PremiumGrade Hand Crimp Tool for Avikrimp and Insulkrimp Terminals and Splices, 22-10 AWG and 6.0-0.5mm^2 (Rings, Spades, Hooks, Block Spades and Flanged Spades)	640010100
Crimp Head for the AT-200 Pneumatic Hand Tool	640050100
ServiceGrade Hand Crimp Tool for Field Repair only, for production use our PremiumGrade Tool	640160036

Downloaded from Arrow.com.