




REV.	DATE	DESCRIPTION
NC	01/28/99	INITIAL RELEASE
A	10/09/06	UPDATE DRAWING FORMAT
B	01/28/08	REVISE O-RING SLOT ORIENTATION



8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex								
7						DRAWN	G.R.S.							01/28/08		
6	HEX NUT	BRASS	NICKEL	1		CHECKED										
5	LOCK WASHER	BRASS	NICKEL	1		ISSUED			PART DESCRIPTION							
4	GASKET	SILICONE	RED	1		SHEET	1 OF 1		N BULKHEAD RECEPTACLE							
3	CONTACT PIN	PHOS. BRONZE	GOLD	1					—							
2	INSULATOR	TEFLON	NATURAL	1					PART NO.							
1	BODY	BRASS	NICKEL	1					172185							
DESCRIPTION		MATERIAL	FINISH	QTY	CAD FILE		C:/172/172188.DWG		DWG. NO.	172185.DWG	REV.	B	SIZE	A	SCALE	NA