
Part Number : 1300350008
Product Description : DeviceNet Power Monitor Inline with LEDs, 5 Pole, Female to Male
Series Number : 130035
Status : Obsolete
Product Category : Industrial Tees and Splitters
Engineering Part Number : 115011A-PM-3



Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Product not active
China RoHS	Product not active
EU ELV	Product not active
Low-Halogen Status	Product not active
REACH SVHC	Product not active
EU RoHS	Product not active

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

Obsolete

Downloaded from Arrow.com.

General

Status	Obsolete
Category	Industrial Tees and Splitters
Series	130035
Description	DeviceNet Power Monitor Inline with LEDs, 5 Pole, Female to Male
IP Rating	IP67
Product Name	DeviceNet Trunk
Type	Diagnostic Tee
UPC	78678853318

Electrical

Current - Maximum per Contact	8.0A
Voltage - Maximum	30V AC

Physical

Color - Cable Jacket	Gray
Drop Connector	N/A
Drop Gender	N/A
Keyway	Single
LED Indicator	Blue, Green, Red, Yellow
Left Trunk Connector	Mini-Change
Left Trunk Gender	Female
Leg 1 Length	N/A
Leg 2 Length	N/A
Material - Cable Jacket	N/A
Material - Connector Body	TPE
Material - Coupling Nut	Black Epoxy Coated Zinc
Net Weight	958.000/g
Poles	5
Right Trunk Connector	DeviceNet
Right Trunk Gender	Male
Temperature Range - Operating	-20° to +80°C

Obsolete

Downloaded from Arrow.com.