

WXP90

Item No: T0052922499N
Hybrid soldering iron 90 W, 24 V with Power Response Heating Technology

KEY FEATURES

- Intelligent hybrid soldering iron 90 W, 24 V
- For small and medium components with high energy demand
- For challenging solder jobs with WX stations
- Parameter memory such as standby temperatures, automatic switch-off time
- Reduces total costs of ownership due to motion sensor
- Visual process control through LED signal function
- Interchangeable heating element including XNT soldering tip provides flexibility
- Interchangeable XNT soldering tips at low cost prices
- Power Response heating technology with improved sensor position
- WSR 200 Safety rest

Downloaded from Arrow.com.

TECHNICAL DATA

Approximate Heating Time (50–350 °C/120–660 °F)	7 sec
Barrel	T0058768724
ESD Safe	Yes
Integrated Direct Extraction	FE Attachment with tube Ø 4.5 mm T0052918599
Power	90 W
Safety Rest	WSR200
Supply Unit	WX1 WX2 WXA2 WXD2 WXR3 WXsmart
Temperature Range (Depends on Tool)	93 - 454°C
Temperature Range °C	100 - 450 °C
Temperature Range °F	200 - 850 °F
Tip Range	XNT
Tip Type	XNT
UPC	037103311573
Voltage	24V
Works With	WX1 WX2 WXA2 WXD2 WXR3
Weight (Catalog)	0.07 kg
Product Family	WX Soldering Irons

Downloaded from Arrow.com.