**Part Number :** 1301500212
**Product Description :** 60 Amp Watertite Pin and Sleeve Receptacle with Flip Lid, 3 Pole/4 Wire, 250V, Blue
**Series Number :** 130150
**Status :** Active
**Product Category :** Wiring Devices
**Engineering Part Number :** 460R9



## Documents and Resources

### Drawings

1301500212_sd.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | Not Reviewed per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Reviewed per IEC 61249-2-21 |
| REACH SVHC | Not Reviewed per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS | Not Reviewed per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Downloaded from Arrow.com.

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | Wiring Devices |
| Series | 130150 |
| Description | 60 Amp Watertite Pin and Sleeve Receptacle with Flip Lid, 3 Pole/4 Wire,  250V, Blue |
| Comments | IEC Configuration 309-1/309-2 |
| IP Rating | IP67 |
| NEMA Configuration | N/A |
| Product Name | Watertite |
| Specialty | Pin and Sleeve |
| Type | Receptacle |
| UPC | 78678872694 |

### Agency

| | |
|---|---|
| UL | E145923 |

### Electrical

| | |
|---|---|
| Current - Maximum per Contact | 60.0A |
| GFCI | No |
| Voltage - Maximum | 250V |

### Physical

| | |
|---|---|
| Cord Type | N/A |
| Flange | Yes |
| Flip Lid | Yes |
| Gender | Female |
| Length | 241.30mm (9.500") |

Downloaded from Arrow.com.

| | |
|---|---|
| Lighted Connector | No |
| Locking Blade | No |
| Poles | 3-pole/4-wire |
| Receptacle Type | Single |



Downloaded from Arrow.com.