

Protect It! 7-Outlet Surge Protector, 25 ft. Cord, 2160 Joules, Black Housing

MODEL NUMBER: **SUPER725B**



Safeguard your workstation or home electronics against surges, spikes and line noise. Ideal for protecting your computer, printer, scanner, external hard drive and other sensitive electronics.

Description

Perfect for your home or office workstation, the SUPER725B Protect It!® 7-Outlet Surge Protector features a surge suppression rating of 2160 joules to defend your sensitive electronic components against strong surges and spikes.

The SUPER725B includes full normal mode (H-N) and common mode (N-G/H-G) line surge suppression, as well as technology that filters out disruptive EMI/RFI line noise, preventing interference from disrupting your electronics and inflicting damage or data loss.

Your computer and peripherals plug into seven NEMA 5-15R outlets. Two outlets are mounted on the side to let the SUPER725B accommodate three bulky transformers without blocking adjacent outlets.

Integrated 15-amp circuit breaker protects all outlets against dangerous overloads. On/off switch provides one-touch control over connected equipment. A green LED indicates protection status, while a red LED assures that your wall outlet is properly grounded.

The 25-foot (7.6-meter) AC power cord allows the SUPER725B to reach distant outlets, while its right-angle NEMA 5-15P plug allows equipment and furniture to be moved flush against the wall to save space. Keyhole slots incorporated into the bottom panel provide convenient wall or desk mounting options for the black plastic housing.

Features

2160-Joule Surge Protection for Home or Office Electronics 2160-joule rating protects your computer, printer, scanner, external hard drive and other sensitive electronic components against even the strongest surges and spikes
Backed by \$75,000 Ultimate Lifetime Insurance for any connected components damaged by power surge (U.S., Canada and Puerto Rico only)
Full normal mode (H-N) and common mode (N-G/H-G) line surge suppression
Filters out disruptive EMI/RFI line noise that can cause equipment damage or data loss
Exceeds IEEE 587 Category A and B surge suppression specifications

7 Outlets Accept Wide Range of Electronic Devices 7 NEMA 5-15R AC outlets accept most computers and peripherals
Unique side-outlet design accommodates 3 bulky transformers without blocking other outlets

Premium Safety Features Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required
LEDs show grounding and protection status at a glance

Fits Effortlessly Into Your Workstation 25 ft. AC power cord long enough to reach distant outlets
Space-saving right-angle NEMA 5-15P plug allows furniture and equipment to move flush against the wall
Keyhole slots on bottom panel provide convenient wall or desk mounting options
Black plastic housing

Highlights

- 7 NEMA 5-15R outlets, including 3 for bulky transformers
- Surge suppression rating of 2160 joules
- Filters out threatening EMI/RFI line noise
- 15A resettable circuit breaker prevents dangerous overloads
- 25 ft. AC power cord with right-angle NEMA 5-15P plug

Package Includes

- SUPER725B Protect It! 7-Outlet Surge Protector, 25-ft. (7.62 m) Cord, Black Housing
- Owner's manual



Powering Business Worldwide

TRIPP LITE
SERIES

designed for long life

Specifications

OVERVIEW	
UPC Code	037332189844
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Plug Features	Right Angle (36D)
Input Cord Gauge Type	14 gauge; SJT
Input Cord Gauge (AWG)	14
Voltage Compatibility (VAC)	120
Maximum Surge Amps	144000
Input Plug Type	NEMA 5-15P
Input Cord Details	SJT
Input Cord Length (ft.)	25
Right-Angle Plug	Yes
Input Cord Length (m)	7.62
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(7) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(4) Yes
Outlet Orientation	Single row of 5, plus 2 side mounted outlets
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Switches	Two position on/off power switch
Diagnostic LED Details	Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	2160



Powering Business Worldwide

TRIPP LITE
SERIES

AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
UL1449 Let Through Rating	330 L-G, 400 L-N, 400 N-G
EMI / RFI Filtering	Up to 20 dB
Automatic Shut-Off	Yes
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
PHYSICAL	
Material of Construction	Plastic
Power Cord Color	Black
Housing Color	Black
Mounting Holes or Slots	Yes
Slot or Hole Mount Measurement (Center to Center)	Distance between slots = 70 mm; Distance between slot height = 24 mm
Outlets Measurement (Center to Center)	Between Standard Outlets = 29mm; Between Transformer Outlets = 48mm
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	12.40 x 8.27 x 1.77
Shipping Dimensions (hwd / cm)	31.50 x 21.01 x 4.50
Shipping Weight (lbs.)	3.40
Shipping Weight (kg)	1.54
Unit Dimensions (hwd / in.)	1.540 x 2.720 x 10.300
Unit Dimensions (hwd / cm)	3.91 x 6.91 x 26.16
Unit Weight (lbs.)	2.89
Unit Weight (kg)	1.31
Input Cord Color	Black
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	14° to 122°F (-10° to 50°C)
Operating Humidity Range	10% to 90% RH
Storage Humidity Range	5% to 95% RH
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No



Powering Business Worldwide

TRIPP LITE
SERIES

Antimicrobial	No
STANDARDS & COMPLIANCE	
Product Certifications	CAN/CSA-C22.2 No. 269.3 (Canada); CAN/CSA-C22.2 No. 308 (Canada); cUL Listed; NOM (Mexico); UL 1449; UL 1363; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$75,000 Ultimate Lifetime Insurance

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.