



**Part Number :** [2061386014](#)

**Product Description :** NearStack 100-Ohm Angle-Exit-to-NearStack 100-Ohm Angle-Exit Cable Assembly, Pull Bale, Without Positive Lock, 32 Circuits, 8 Differential Pair, 350.00mm Length

**Series Number :** 206138

**Status :** Active

**Product Category :** High-Speed I/O Cable Assemblies



---

## Documents and Resources

### Drawings

[2061386014 sd.pdf](#)

[2035871100-PK.pdf](#)

### Specifications


[2033160001-AS-000.pdf](#)

[2033160001-000.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	High-Speed I/O Cable Assemblies
Series	206138
Description	NearStack 100-Ohm Angle-Exit-to-NearStack 100-Ohm Angle-Exit Cable Assembly, Pull Bale, Without Positive Lock, 32 Circuits, 8 Differential Pair, 350.00mm Length
Assembly Configuration	Dual Ended Connectors
Connector to Connector	NearStack 100-Ohm-to-NearStack 100-Ohm
Product Name	NearStack 100-Ohm
Type	Internal
UPC	193264767632

### Electrical

Data Rate	56.0 Gbps (PAM-4)
Voltage - Maximum	29.9V AC (RMS)/DC

### Physical

Cable Bundling	None
Cable Length	350.00mm
Circuits (Loaded)	32
Circuits (maximum)	32

Color - Resin	Black
Gender	Receptacle/Receptacle
Lock to Mating Part	No
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Liquid Crystal Polymer
Net Weight	12.516/g
Number of Pairs	8
Orientation	Angle-Exit-to-Angle-Exit
Release Style	Pull Bale
Single Ended	No
Wire/Cable Type	Twinax

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
NearStack 100-Ohm Connectors	<u>203316</u>

---

This document was generated on Apr 12, 2026