



Product Navigation

[Home](#)
[About Us](#)
[Products](#)
[Investor Relations](#)
[News](#)
[Contact Us](#)
[Secure EAX](#)

Circuit Board Indicators

Panel Mount Indicators

Solid State Lighting

Traffic Signals

Vehicle Lighting

Rail

Obstruction Lighting

Hazardous Area Lighting

Heliport Lighting

how to purchase

[sales contacts](#)
[stock check](#)

search

Product Line Search

Please select a Product Line to search.

Circuit Board Indicators

find

Part # / Text Search

Part No.:

Text Search:

search

quick links

Dialight Corporate Video

Presentation at LightFair 2007 - "Presentation of White LEDs" : by Ian Ferguson, Georgia Tech in conjunction with Dialight Corp. [View PDF File](#)

Application Notes
FAQs

Dialight Ltd (UK)
Dialight Garufo
Dialight BLP
LumiDrives

Circuit Board Indicators - Through Hole Indicators

P/N# **5680720441F**

Rectangle Lens

Description	2X4 mm Quad-Level CBI X-Y/G-Y/G-R/G
Package Options	5 Pieces Per Bag
Product Type	Through Hole Indicators
Sub Product Type	with Quad Level Housing
Configuration	Rectangle Lens
Viewing	Right Angle
Test Current (mA)	10mA

Absolute Maximum Ratings (Ta = 25 °)

Distributor Stock Check

Check stock with our distributors now.

5680720441F

[check stock](#)

Operating Characteristics

LED Position	Found in position(s): 1	Found in position(s): 2,3	Found in position(s): 4
Color	Blank	Yellow / Green	Red / Green
Lamp Type	Single Color	Bi-Color / Bi-Color	Bi-Color / Bi-Color
LED Type			
Intensity Min (mcd)		2.5 / 2.5	2.5 / 3.7
Intensity Typ (mcd)		4.3 / 6.3	4.7 / 10.0
Intensity Max (mcd)			
Fwd Voltage Min			
Fwd Voltage Typ			
Fwd Voltage Max			
Dom Wavelength Min (nm)		587 / 569	621 / 569
Dom Wavelength Typ (nm)			
Dom Wavelength Max (nm)			
Power Dissipation Max (mW)		60 / 100	100 / 100
Backlighting		Yes / Yes	
Pitch Between Vertical		5.08 / 5.08	2.54 / 2.54
Pitch Between Horizontal			
Lum Intensity Min			
Lum Intensity Typ			
Lum Intensity Max			