





Printed board layout component side



A	09 66 211 6501	M3	2						 All Dim. in mm Orig. Size DIN A 4	D-sub, 15 poles, female, straight, with solder pins 2.9, and nuts.	Maßstab/ Scale 1,5:1	
	09 66 211 7501	M3	3				Detail.	05/03/02				CV
	09 66 211 5501	M3	0,76 µm Au				Insp.					
	09 66 211 6502	4-40 UNC	2				Stand.					
	09 66 211 7502	4-40 UNC	3									
	09 66 211 5502	4-40 UNC	0,76 µm Au	29723	05/03/02	CV						
	Part number	Nut thread	Performance level	Mod.	Dat.	Name	HARTING EURL F-95972 Paris			TB 09 66 211 x50x Sub.	Blatt/ Page 2	



						Dat. 05/03/02 Name CV		All Dim. in mm Orig. Size DIN A 4	D-sub, 15 poles, female, straight, with solder pins 2.9, and screw locks.	Maßstab/ Scale 1,5:1
						Insp. Stand.				
09 66 211 6503	4-40 UNC	2				HARTING EURL F-95972 Paris		TB 09 66 211 x50x Sub.	Blatt/ Page 3	
09 66 211 7503	4-40 UNC	3								
09 66 211 5503	4-40 UNC	0,76 µm Au	29723	05/03/02	CV					
Part number	Screw lock thread	Performance level	Mod.	Dat.	Name					