

Part Number : 190440164
Product Description : Krimptite Ring Tongue Terminal for 16-14 AWG, Stud Size 10, 19.94mm Length, Mylar Tape Carrier
Series Number : 19044
Status : Active
Product Category : Ring and Spade Terminals
Engineering Part Number : B-128-10HDT

Documents and Resources

Drawings

190440164_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

Downloaded from Arrow.com.

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19044
Description	Krimptite Ring Tongue Terminal for 16-14 AWG, Stud Size 10, 19.94mm Length, Mylar Tape Carrier
Comments	Heavy Duty
Keyword	Ring Terminal, Ring Terminals
Product Name	Krimptite
Style	Ring
Type	Ring Terminal, Metric Ring Terminal
UPC	800753051102

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed
Insulation	None
Material - Plating Mating	Tin
Net Weight	1.755/g
Packaging Type	Adhesive Tape on Reel

Downloaded from Arrow.com.

Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Stud Size	10 (M5)
Termination Interface Style	Crimp or Compression
Wire Size (AWG)	14, 16
Wire Size mm^2	1.30-2.00

Application Tooling

Global

Description	Part Number
ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press	190270088
Mini-Mac Applicator	638851000

Downloaded from Arrow.com.