

REV	
NC	DT04-12PA-BE04


REVISIONS			
SYM	DESCRIPTION	DATE	APPROVED
NC	NEW RELEASE PER E.O. P17758	6-11-02	RDR





-E- DESIGNATES REDUCED DIAMETER WIRE SEAL

CONTACT SIZE	MIN. INSUL O.D.	MAX. INSUL O.D.	WIRE RANGE [mm²] REF ONLY (3)
16	.053 [1.35]	.120 [3.05]	14-20 AWG [2.0-0.5]



4. THIS RECEPTACLE MATES WITH THE DT06-12SA-**** PLUG (**** = ALL MODIFICATIONS). CONSULT FACTORY FOR MODIFICATIONS.

(3.) FOR CONTACTS AND WIRE PERFORMANCE AND APPLICATION CHARACTERISTICS SEE ENVELOPE DRAWING 0425-015-0000 AND 0425-017-0000.

2. DIMENSIONS ARE ±.025[0.64] UNLESS OTHERWISE SPECIFIED.

1. DIMENSIONS ARE IN INCHES [MILLIMETERS].

NOTES:

	SIGNATURE & DATE
DR	T. YOHANNES 08MAY02
CHK	5/28/02
PE	5/8/02
APPD	5-8-02
SCALE	NONE WT

12 WAY RECEPTACLE
EXTRA KEY W/ CAP
-BE04 MOD.
-A- ARRANGEMENT
COLOR:BLACK
DT SERIES

ENVELOPE

CP — MATL. CODE

The Deutsch Company
DEUTSCH I.P.D.
3850 INDUSTRIAL AVE.
HEMET, CALIF. 92545

B — DWG SIZE

DT04-12PA-BE04

CODE 11139 — SHEET 1 OF 1

Downloaded from Arrow.com.