

MICRO SWITCHFREEPORT ILLINOIS, U S A
A DIVISION OF HONEYWELL INC
FED. MFG. CODE 91929**SWITCH - BASIC**CATALOG LISTING
BE-R2420-A2**BE-R2420-A2****M**DRAWING
NUMBER**X****X**

ISSUE

3

REPLACES

RELEASE NO. PR-17856

CHECK

REVISIONS

A	CO-73287-J
	J A L
	22 NOV 93
B	CO-77588
	MAM
	29 MAR 94

CHECK

28 DEC 89


DRAW

CHECK

WJM 28 DEC 89

0-52848-B


DRAWN

**NOTES**

- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .139 MAX DIA ON 1.000 ± .002 CENTERS
- 2 - SWITCH MATERIALS WILL WITHSTAND TEMPERATURE OF 250°F

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION

**CHARACTERISTICS**

OPERATING FORCE ----- 11-17 OZ

RELEASE FORCE ----- 10 OZ MIN

DIFFERENTIAL TRAVEL --- .0015-.0025

OVERTRAVEL ----- 010 MIN

ELECTRICAL DATACONTACT ARRANGEMENT
S P D T25A-125, 250, OR 480 VAC
3/4 HP-125 VAC; 1 1/2 HP-250 VAC
PILOT DUTY 375 VA-125, OR 250 VAC
60/75°C (C_u)**SCALE FULL****DO NOT SCALE PRINT**UNLESS OTHERWISE SPECIFIED
TOLERANCES ARE

ONE PLACE (.01) ± .030

TWO PLACE (.001) ± .015

THREE PLACE (.0001) ± .004

ANGLES ±

WEIGHT .063 LB