

Connector Location A


Connector Location B




X
male



Loading-Plan



Y
female



length in "1m" step		
	40	XXX=400
	39	XXX=390
	.	.
	.	.
	12	XXX=120
	11	XXX=110
length in "0.1m" step	10	XXX=100
	9.9	XXX=099
	9.8	XXX=098
	.	.
	.	.
	0.4	XXX=004
	0.3	XXX=003
	0.2	XXX=002
	0.1	XXX=001
Step	**a [m]**	**XXX**

a [m]	Tolerance
4.0 to 40	±1%
0.1 to 3.9	+0.04

- Protection level: IP67
- Temperature range: -30°C ... +60°C

PVC violet, 2xAWG22	21348889486XXX
Type of cable	**Part no.**

All Dimensions in mm | Tech. Character. | Free size tol. | According to production drawing

All rights reserved

Department HCS - RO

HARTING Customised Solutions
D-32339 Espelkamp

Created by	Inspected by	Standardisation	Date	State
STOCHECIC Stocheci	COSTEA Costea	MUNTEANV Muntean	2018-12-14	Final Release

Title: M12 Cable Assembly B-cod st/st m/f

Doc-Key / ECM-Nr.: 100579391/UGD/009/B 500000144878

Type: TB | Number: 21348889486XXX | Rev.: B | Page: 1/1

Downloaded from Arrow.com.

A3