Datasheet for part number DDMMY-50P

Our Catalog Part Number: DDMMY-50P
Our Global Manufacturing Part Number: 051526-0067
Brand: Cannon Product Category: D Sub Product Line: D Sub Series: D*M

Product Datasheet	
General	D*M High reliable D-Sub Connectors
Wire Gauge Range AWG	AWG 20-28
Mating Cycles	500
Contact Arrangement	50 contacts size 20
Dielectric Withstanding Voltage	1000 VAC at sea level
Current Rating	7.5 A max
Contact Resistance	7.5 milli Ohm max
Operating Temperature	-55°/+150°
Salt Spray Test	48 hours {96 Hrs for Stainless Steel}
Shell Material	Steel
Shell Finish	Yellow chromate over zinc
Insulator Material	Thermoplastic, type PCT UL 94V-0
Insulator Color	black
Gender	Pin
Contact Type	Solder Pot
Contact Material	copper alloy
Contact Finish	50 microinch gold over 40 microinch nickel
Hardware	Dual Float Mount

Specifications and dimensions subject to change.

Downloaded from Arrow.com.