**Part Number :** 1300170029
**Product Description :** Mini-Change Field Attachable, Male Connector, 5 Pole, Cable Range: 5.08-11.43mm Outside Diameter with External Threads
**Series Number :** 130017
**Status :** Active
**Product Category :** Industrial Connectors
**Engineering Part Number :** 1A5006-34



## Documents and Resources

### Drawings

1300170029_sd.pdf

STEP AP242

SOLIDWORKS

Creo

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Contains Lead per D(2025)7771-DC (04 Feb 2026) SCIP:b883f2d4-d7a1-49bd-9f9b-ad931ed08974 |
| EU RoHS | Compliant with Exemption 6(c) per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D

Downloaded from Arrow.com.

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | Industrial Connectors |
| Series | 130017 |
| Description | Mini-Change Field Attachable, Male Connector, 5 Pole, Cable Range: 5.08-11.43mm Outside Diameter with External Threads |
| Approvals | cCSAus certified |
| IP Rating | IP67 |
| Product Name | Mini-Change |
| Type | Field Attachable Connector |
| UPC | 78172553065 |

### Agency

| | |
|---|---|
| CSA | LR6837 |

### Electrical

| | |
|---|---|
| Current - Maximum per Contact | 8.0A |
| Voltage - Maximum | 600V AC/DC |

### Physical

| | |
|---|---|
| Cable Diameter | 5.08-11.43mm (.200-.450") |
| Coupling Type | External Thread |
| Diagnostics / LEDs | No |

Downloaded from Arrow.com.

| | |
|---|---|
| Diagnostics Port | No |
| Gender | Male |
| Keyway | Single |
| Material - Connector Body | Nylon |
| Material - Contact | Copper Alloy |
| Material - Coupling Nut | Nickel-plated Brass |
| Material - Plating Mating | Gold |
| Net Weight | 59.874/g |
| Orientation | Straight |
| Poles | 5 |
| Temperature Range - Operating | -20° to +80°C |
| Wire Size (AWG) | 15 to 24 |



Downloaded from Arrow.com.