

MICRO SWITCH

A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR COMPANY
FREEPORT, ILLINOIS

FED. MFR. CODE 91929

SWITCH-BASIC

CATALOG LISTING

DT-2R-B6

(M) DT-2R-B6
ISSUE 3

REPLACES

RELEASE NO.

CHECK

CHECK

CHECK

DT-2R-B6

M


DRAWING
NUMBER

12

ISSUE

REVISIONS

A	CO15451	L S D	17 JAN 61
B	CO17707	R E R	14 MAR 63
C	CO17725	L S D	25 JUN 63
D	CO 21667	M B F	30 JUN 66
E	CO-30659	S R H	31 MAY 72
F	CO37528	C J H	31 AUG 76
G	CO 38759	R E R	25 MAY 77
H	CO 39046	G A S	16 SEPT 77
J	CO80154	JAK	28 FEB 95



6-32 NC-2 X .188 REF
SCREW (NO. 5 PAN HEAD) (6)

NOTE -

△ MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF
.139 MAX DIA ON 1.000 ± .002 CENTERS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

OPERATING FORCE — — — — — 12-20 OZ
RELEASE FORCE — — — — — 2 OZ MIN
DIFFERENTIAL TRAVEL — — — .040-.060
OVERTRAVEL — — — — — .005 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
D P D T

UNDERWRITERS' LAB. INC. LISTED RATING
-L59- 10 A-125 OR 250 VAC
0.3 A-125 VDC; 0.15 A-250 VDC

DWL



SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE
SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCES ARE:
ONE PLACE (.0) ± .090
TWO PLACE (.00) ± .015
THREE PLACE (.000) ± .005
ANGLES ±

WEIGHT

FO-50378

DRAWN

LSD 17 JAN 61