

Representative Image

## Catalog No. L-8-18-0-M

**Description: CBL TIE 18LB 8 IN UV BLK 1-PC BULK**

**UPC No 728494917702**

**Home > Wire & Cable Management > Catamount > Cable ties**

Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F), Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, Length of 203mm (7.99 Inches), Width of 2.5mm (0.10 Inch), Thickness of 1.2mm (0.05 Inch), Tensile Strength Rating of 80 Newtons (18 Pounds), Bulk Pack

### Descriptors

| | |
|---|---|
| Category | Cable ties |

### Specifications

| | |
|---|---|
| Material | Nylon/Polyamide 6.6 Weather Resistant |
| Color | Black |
| Lock Mechanism | Plastic Pawl |
| Tensile Strength | 18 pounds , 80 newtons |

### Classifications

| | |
|---|---|
| Brand Name | Catamount |
| Standard | UL E49405 |

### Dimensions

| | |
|---|---|
| Width | 0.1 in , 2.54 mm |
| Length | 7.99 in , 203 mm |
| Thickness | 0.05 in , 1.2 mm |
| Bundle Diameter | 0.0625 to 2 in , 1.59 to 50.8 mm |

### Compliance and Certifications

| | |
|---|---|
| RoHS | RoHS3 Compliant |
| REACH | REACH 247 Compliant |
| TSCA | TSCA Section 6(h) Compliant |

| | |
|---|---|
| ETIM | EC000046 Cable tie |
| Band width | 2.5 mm |
| Length belt/tape/tie | 203 mm |
| Length belt/tape/tie | 8 inch |

by ABB



Downloaded from Arrow.com.

| | |
|---|---|
| ETIM | EC000046 Cable tie |
| Tie thickness | 1.2 mm |
| Tie thickness | 0.05 inch |
| Min. holding force | 80 N |
| Model | Internal toothing |
| Band closure | Plastic lip/-cam |
| Material | Plastic |
| Material quality | Polyamide (PA) |
| Surface protection | Untreated |
| Halogen free | Y |
| Colour | Black |
| Transparent | N |
| Reflective (fluorescent) | N |
| Text strip | None |
| Solvable fastener | N |
| MIL approval | N |

**Certification/Standard**

| CLASS | File Number | Class | CCN | Certificate Number | Library Number |
|---|---|---|---|---|---|
| UL | E49405 | N/A | N/A | N/A | N/A |



Downloaded from Arrow.com.