Part Number : 1301030016
Product Description : Watertite Wet Location Incandescent Hand Lamp, 100W with Screw Release Grounded Guard, Cord Type 16/3 SOOW, 15.24m (50.0') Cord Length
Series Number : 130103
Status : Active
Product Category : Lamps and Lights
Engineering Part Number : 1203B163



Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Lamps and Lights
Series	130103
Description	Watertite Wet Location Incandescent Hand Lamp, 100W with Screw Release Grounded Guard, Cord Type 16/3 SOOW, 15.24m (50.0') Cord Length
NEMA Configuration	NEMA 5-15
NEMA Rating	NEMA 4X
Product Name	Watertite
Type	Hand Lamps
UPC	78678861302

Agency

CSA	LR85374

Electrical

Lamp Wattage - Maximum	100W
Lumens	1000
On/Off Switch	No
Voltage (Fixture) - Maximum	120V AC

Physical

Bulb Type	Incandescent
Cord Length - Primary	15.24m (50.0')
Cord Length - Secondary	N/A
Cord Type - Primary	16/3 SOOW
Depth	120.65mm (4.750")
Duty	Wet Location
Guard Included	Yes

Downloaded from Arrow.com.

Guard Type	Grounded, Screw Release
Height	457.20mm (18.000")
Lamp Type	A21
Length	N/A
Material - Globe	Tempered Glass
Material - Guard	#8 Gauge Zinc-plated Steel
Mounting Style	Hand Held
Net Weight	3220.505/g
Outlet	None
Packaging Type	Carton

Downloaded from Arrow.com.