




**HF**  
 Halogen Free


## NOTES:

1. MATERIAL:
  - 1.1 HOUSING: HIGH TEMPERATURE THERMOPLASTIC, UL94V-0, COLOR: BLACK.
  - 1.2. CONTACT: COPPER ALLOY.
  - 1.3. SOLDER PEG: STAINLESS STEEL.
2. FINISH:
  - 2.1 CONTACT:
    - UNDERPLATING NICKEL 50u" MIN OVERALL
    - MATING AREA: GOLD PLATING, THICKNESS SEE TABLE
    - SOLDER AREA: GOLD FLASH 1u" MIN.
  - 2.2 SOLDER PEG:
    - UNDERPLATING NICKEL 50u" MIN OVERALL
    - 80u" MIN MATTE TIN ON SURFACE
3. DATE CODE : YYWWDLX
  - YY: YEAR (09: 2009)
  - WW: WEEK (25: THE 25TH WEEK)
  - D: DAY (1~7: SUNDAY~SATURDAY)
  - L: LINE NUMBER OF ASSEMBLY (A: LINE A)
  - X: D OR N (D: DAY; N: NIGHT)
4. PRODUCT SPECIFICATION SEE FCI GS-12-1195
5. PART NUMBER DESCRIPTION:
  - 10128793-00XRLF




LF: LEAD FREE &amp; RoHS COMPLIANCE

PACKAGE CODE:


R: TAPE &amp; REEL PACKING

PLATING CODE:

- 1: GOLD FLASH ON CONTACT AREA
- 4: 15u" Min GOLD ON CONTACT AREA
- 5: 30u" Min GOLD ON CONTACT AREA



MATING ANGLE ILLUSTRATION



30u" Au	10128793-005RLF
15u" Au	10128793-004RLF
GOLD FLASH	10128793-001RLF
CONTACT AREA	FCI P/N

mat'l. code				surface	tolerance	projection	product family			
ltr	ecn no	dr	date	tolerances unless otherwise specified		mm	title			
A	BF		2013-04-18	angles	.X					
B	ELX-T-19318	TAI	2014-11-10		.XX					
C	ELX-T-20858	TAI	2015-05-11	X"±2"	.XXX					
				dr	BEER FU	2013-05-02	<div>FCI</div> dwg no 10128793 sheet 1 of 3 size A4			
				enr	BEER FU	2013-05-02				
				chr	BEER FU	2013-05-02				
				appd	BEER FU	2013-05-02				
sheet index	revision	C	C	C			type Customer Drawing			
	sheet	1	2	3						

~~PB~~

ing	B
-----	---