



P/N 010505030

External dimensions: 45 x 50 x 30 mm


Weight: 91 g

	DIN rail length in mm	
	max. fitting length in mm	
	Earthing rail clamp	
	Mounting plate (thickness in mm)	
	External mounting brackets	
	External hinge* set	
•	EMC version	
	Internal hinge* set	
•	SWB / SBG / SBGL Corr.protection	
•	Allen lid screws	
	Silicone lid seal	
•	Sealable lid screws in steel	
	Turn bolt fastener on request	
	Quick lock	

Maximum number of cable glands to DIN 50262*								
								
M	Corner dim.	Side		PG	Corner dim.	Side		PG
		A B	C D			A B	C D	
12	17.25	2	1	7	17.25	2	1	7
16	25.30			9	21.85	1		9
20	27.60			11	25.30			11
25	37.95			13.5	27.60			13.5
32	48.30			16	31.05			16
40	60.95			21	37.95			21
50	69.00			29	48.30			29
63	74.75			36	60.95			36
				42	69.00			42
				48	74.75			48



* = Conical form tapering downwards
Free dimensions-tolerance to GTA 13/5 DIN 1688



DATE	17 MAY 2017	7330 Executive Way Frederick, MD 21704 (301) 696-9411 voice (301) 696-9494 fax	
SHEET	1		
DESCRIPTION		ENCLOSURE, STANDARD, ALUMINUM 45 X 50 X 30MM, RAL 7001	
SIZE	DRAWING NUMBER	REV	
A	010505030	-	