



COIL: @ +25 °C

| | |
|---|---|
| RESISTANCE | 600 OHMS ± 10% |
| NOMINAL VOLTAGE | 26.5 VDC |
| MUST OPERATE | 13.4 VDC |
| MUST RELEASE | 1.5 VDC |

ENVIRONMENT:


VIBRATION 10 CPS TO 2000 CPS @ 20 g's

SHOCK 100 g's 6 MS. DURATION

TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE 4 MS MAX.
RELEASE 3 MS MAX.
CONTACT BOUNCE 3 MS MAX.

# CUSTOMER DATA SHEET




CONTACT RATING: 4 AMPS 30 VDC
1 AMP 115 VAC 400 HZ
100,000 OPERATIONS MIN.

DR. R.B. 1/6/95 CK. 10/5/95 JMR

COMMUNICATIONS INSTRUMENTS, INC.

CUST. HI-G
CUST. NO. 2HA-2A-126

TYPE "HFW" RELAY

# HFW4A1201S01

Downloaded from Arrow.com.