

6

5

4

3





2

1

APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	10/25/22	



SPECIFICATIONS:

Material:

Insulator: Hi-Temp Thermoplastic, rated UL 94V-0

Insulator color: Black

Contacts: Brass

Plating:

30u" Gold over Nickel underplate on contact area

Matte Tin over Nickel underplate on solder tails

Electrical:

Current rating: 1 Amp

Contact resistance: 20 mohms max

Insulation resistance: 1,000 Mohms min

Dielectric withstanding voltage: 500 VAC for 1 minute

Temperature Rating:

-40°C to +105°C

Environmental:

Lead free, RoHS compliant



PACKAGED ON PLASTIC TUBE

Positions: 04 thru 100

A = .050 [1.27] x No. of Positions per Row + .012 [0.30]

B = .050 [1.27] x No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ± .10	ØX ± .10
.XX ± .020	ØXX ± .015
.XXX ± .015	ØXXX ± .010

DRAWN	LH	10/25/22
CHECKED	NP	10/25/22
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN PERMISSION FROM ADAM TECH

ADAM
TECH

 909 Rahway Avenue,
 Union, NJ 07083
 Phone: 908-687-5000
 Fax: 908-687-5710

TITLE	.050" X .050" PIN HEADER, DUAL ROW		
SIZE	30u" SEL GOLD MATTE TIN PLATED STRAIGHT, SMT		
PART NO.	HPH2-B-XX-SGMA-SMT-30-KS1-PT		
REV.	-		
REF:	S00111C	SCALE: NTS	SHEET 1 OF 1

6

5

4

3

2

1