



Part Number : [192020054](#)

Product Description : NylaKrimp Butt Splice for 8 AWG Wire, Carton

Series Number : 19202

Status : Active

Product Category : Splices

Engineering Part Number : D-754



Documents and Resources

Drawings

[192020054_sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

[Industry Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Splices
Series	19202
Description	NylaKrimp Butt Splice for 8 AWG Wire, Carton
Product Name	NylaKrimp
Style	Standard
Type	Butt Splice
UPC	800753048294

Agency

CSA	LR18689
UL	E32244

Electrical

Voltage - Maximum	300V
-------------------	------

Physical

Barrel Type	Closed - Brazed
Color - Resin	Red
Flammability	94V-2
Insulation	Nylon (PA)
Material - Metal	Copper
Material - Plating Mating	Tin

Material - Plating Termination	Tin
Net Weight	5.122/g
Packaging Type	Carton
Temperature Range - Operating	-55° to +105°C
Wire Insulation Diameter	6.73mm max.
Wire Size (AWG)	8

Application Tooling

Global

Description	Part Number
PremiumGrade Hand Crimp Tool for 8-2 AWG Terminals	<u>640013900</u>
Crimp Tool Kit for 8 AWG Insulated Ring Terminals	<u>640017670</u>

This document was generated on Apr 29, 2026