



Part Number : [1300950137](#)
Product Description : Heavy Duty Wire Mesh Pulling Grip, Double Weave, Rotating Eye, Standard Mesh Length 0.864m (34.00"), Approximate Break Strength 7438.92kg (16400 lbs)
Series Number : 130095
Status : Active
Product Category : Cable Grips
Engineering Part Number : 35882



Documents and Resources

Drawings

[1300950137_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Cable Grips
Series	130095
Description	Heavy Duty Wire Mesh Pulling Grip, Double Weave, Rotating Eye, Standard Mesh Length 0.864m (34.00"), Approximate Break Strength 7438.92kg (16400 lbs)
Product Name	Heavy Duty
Type	Pulling Grip
UPC	78678835882

Agency

CSA	LR32159
-----	---------

Physical

Approximate Break Strength	7438.92kg (16400 lbs)
Bale Length	N/A
Body Style	Straight
Cable Diameter	38.10-50.55mm (1.500-1.990")
Color - Grommet	N/A
Eye Diameter	1 3/8"
Eye Type	Rotating
Gender	N/A
Material - Body	N/A
Material - Grip	Galvanized Steel
Mesh Length	0.864m (34.00")
Net Weight	1240.923/g
Number of Holes	N/A

O-Ring	N/A
Thread Size	N/A

This document was generated on May 21, 2026