



Pushing Performance

Han Multi module, male



Image is for illustration purposes only. Please refer to product description.

Part number	09 14 004 4501
Specification	Han Multi module, male
HARTING eCatalogue	https://b2b.harting.com/09140044501

Identification

Category	Modules
Series	Han-Modular®
Type of module	Han® Multi module

Version

Gender	Male
Number of contacts	4
Details	Please order contacts separately.
Details	When removing the contacts, the two-piece module can be opened using a 7mm screwdriver. This destroys the module.

Technical characteristics

Rated current	1.5 A
Rated voltage	50 V
Insulation resistance	$>10^{10} \Omega$
Limiting temperature	-40 ... +125 °C
Mating cycles	≥ 500

Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant



Pushing Performance

Material properties

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Specifications	EN 60664-1 IEC 61984
Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076

Commercial data

Packaging size	2
Net weight	7.12 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440218 Module for industrial connectors (data)