

JOIN OUR NEWSLETTER



SEARCH



BROWSE BY
**PRODUCT
CATEGORY**



BROWSE BY
**DEVICE
MANUFACTURER**



ADVANCED
**INDUSTRIAL
SEARCH**

[Home](#) / [UL10HA](#)



hover to zoom; click to enlarge

PART#: UL10HA

Chemistry:	Zinc Air
Voltage:	1.35
Capacity:	mAh
Measurements:	1.8" x 3.5" x 0.17" 45.72mm x 88.90mm x 4.32mm

[Find a Distributor](#)

Size 10- 6 Pack Carded, Spin Dial, Tabbed

SPECIFICATIONS

Shipping Weight (oz)	0.2000
UPC	760973000000
Length	1.8" (45.72mm)
Width	3.5" (88.90mm)
Height / Diameter	0.17" (4.32mm)
Voltage	1.35
mAh	No
Number of Cells	No
Battery Chemistry	Zinc Air
Rechargeable	Non-Rechargeable
Qty Per Package	6
Type of Cell	Button
Weight	0.2 oz

Compatible Batteries and Devices

[Batteries \(11\)](#)



IMAGES ARE FOR REFERENCE ONLY! Please note that the capacity (mAh) may change without notice. Always consult the product specifications for correct information. Dantona Industries, Inc. is not affiliated in any way with any of the manufacturers listed in this catalog and the batteries sold in this catalog have not been sponsored or approved by any of such manufacturers. Any trademarks or model numbers listed in this catalog are identified for compatibility or cross-reference purposes only.

**CAN'T FIND
THE BATTERY
YOU NEED?**

**CALL US AT
1-800-Dantona
TO SPEAK TO
A BATTERY EXPERT**



**VIEW OUR WIDE
SELECTION OF**

**Custom
Battery
Packs**

[SHOP OUR CUSTOM PACKS](#)

