UPA500T

Provide feedback
Print this page

Products
Discrete
Transistors
Transistor Arrays
UPA500T

Overview Documentation Design Support

Product Spec Order Information Package & Packing

Product Spec

Automotive	-	Package Type	5pin MM
IC (A) @25 °C	0.1	Production Status	In Mass Production
Surge Absorber Diode	NO	Ordering Condition	-
Number of Circuits	2	Downloadable	-
Pt (mW)	300	Feature	Small Signal Transistor Array(Multi-chip)
Application	-	V_{CEO} (V)	50

Back To Top

Order Information

Orderable Part No.	Production Status.	Packing	Environmental	remark
UPA500T-T1-A	Mass Production	-	Pb free	-
UPA500T-AT	Mass Production	-	Pb free	-
UPA500T-T2-A	Mass Production	-	Pb free	-
UPA500T-T2-AT	Mass Production	-	Pb free	-
UPA500T-T1-AT	Mass Production	-	Pb free	-

Back To Top

Package & Packing

p5c3-95-121 fig1080e

Package	
Renesas code	PLSP0005ZD-A
Previous code	P5C3-95-121
JEITA code	SC-74A
Name	MM
Terminal count	5
Terminal pitch (mm)	0.95
Dimensions (mm)	2.9x1.5
Mass (g)[TYP.]	0.013
Mounting height (mm)[MAX]	1.4
Terminal material - Base	Cu alloy
Terminal material - Surface	Sn-Bi or Sn
Drawing Link	p5c3-95-121
Mount pad	fig1080e

Packing	
Packing Tape No dry pack	H2236

Back To Top

©2010-2012 Renesas Electronics Corporation. All rights reserved.

Downloaded from Arrow.com.