



Part Number : [1300700012](#)

Product Description : BradPower A-Size (7/8"-M22)

Power Locking Clip, 33.02mm Diameter

Series Number : 130070

Status : Active

Product Category : Industrial Accessories

Engineering Part Number : 11400A-10



Documents and Resources

Drawings

[1300700012_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

[EU RoHS Certificate of Compliance](#)

[Additional Product Compliance Information](#)

[CE - Declaration of Conformity](#)

[UKCA - Declaration of Conformity](#)

Part Details

General

Status	Active
Category	Industrial Accessories
Series	130070
Description	BradPower A-Size (7/8"-M22) Power Locking Clip, 33.02mm Diameter
IP Rating	N/A
Product Name	BradPower A-Size
Type	Accessory - Locking Clip
UPC	78678882236

Electrical

Current - Maximum per Contact	N/A
Voltage - Maximum	N/A

Physical

Cable Diameter	N/A
Coupling Type	N/A
Diagnostics / LEDs	No
Diagnostics Port	No
Keyway	None
Material - Connector Body	Polyester
Material - Contact	N/A
Material - Coupling Nut	N/A
Material - Plating Mating	n/a
Net Weight	12.000/g
Poles	N/A
Temperature Range - Operating	-20° to +90°C

Wire Size (AWG)	N/A
-----------------	-----

This document was generated on Apr 28, 2026