

BFHE-10/20-8-BF



TE Connectivity has acquired the DIN Rail Terminal Block product range from ABB

Products → Low Voltage Products and Systems → Connection Devices → PLC Wiring Systems
→ PLC Connecting Interfaces

General Information

Extended Product Type:	BFHE-10/20-8-BF
Product ID:	1SNA020802R2000
EAN:	3472599020337
Catalog Description:	BFHE-10/20-8-BF - Connecting Interface
Long Description:	BFHE Two-wire interface for 8 channels with negative common and fuse on each I/O for HE10/20 connector.

Ordering

Minimum Order Quantity:	1 piece
Customs Tariff Number:	85371098

Popular Downloads

Data Sheet, Technical Information:	1SNC127006C0202
Instructions and Manuals:	1SNC127006C0202

Dimensions

Product Net Width:	57 mm
Product Net Height:	75 mm
Product Net Depth / Length:	71 mm
Product Net Weight:	0.102 kg

Technical

Connection Type:	Pluggable - Screw clamp
Pollution Degree:	2
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Wire Stripping Length:	7.5 mm
Recommended Screw Driver:	3.5 mm

Technical UL/CSA

Connecting Capacity UL/CSA:	Stranded 14 AWG
Flammability According to UL94:	V0

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	1SND225028U1000
--	-----------------

Environmental Information:	1SNC127006C0202
-----------------------------------	-----------------

Instructions and Manuals:	1SNC127006C0202
----------------------------------	-----------------

Classifications

Object Classification Code:	X
------------------------------------	---

ETIM 4:	EC001604 - Fieldbus, decentr. periphery - communication module
----------------	--

ETIM 5:	EC002780 - Interface module
----------------	-----------------------------

ETIM 6:	EC002780 - Interface module
----------------	-----------------------------

Container Information

Package Level 1 Units:	1 piece
-------------------------------	---------

Package Level 1 Width:	85 mm
-------------------------------	-------

Package Level 1 Depth / Length:	110 mm
--	--------

Package Level 1 Height:	60 mm
--------------------------------	-------

Package Level 1 Gross Weight:	0.102 kg
--------------------------------------	----------

Package Level 1 EAN:	3472599020337
-----------------------------	---------------

Package Level 2 Units:	20 piece
-------------------------------	----------

Package Level 2 Width:	300 mm
-------------------------------	--------

Package Level 2 Depth / Length:	500 mm
--	--------

Package Level 2 Height:	150 mm
--------------------------------	--------

Package Level 3 Units:	960 piece
-------------------------------	-----------

Product Packing Type:	Box
------------------------------	-----

