



**Part Number :** [1300060542](#)

**Product Description :** Mini-Change A-Size Single-Ended Cordset, 3 Poles, Male (Straight) to Pigtail, 16 AWG, Yellow PVC Cable, 3.66m (12.0') Length

**Series Number :** 130006

**Status :** Active

**Product Category :** Circular Industrial Cordsets

**Engineering Part Number :** 103002A01F120



---

## Documents and Resources


### Drawings

[1300060542 sd.pdf](#)

---

## Product Environment Compliance

### Compliance

|                    |   |
|--------------------|---|
| GADSL/IMDS         | Not Relevant  |
| China RoHS         |  per SJ/T 11365-2006 |
| EU ELV             | Not Relevant  |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21  |
| REACH SVHC         | Contains Lead per D(2025)7771-DC (04 Feb 2026)  |
| EU RoHS            | Compliant with Exemption 6(c) per EU 2015/863   |

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

## Part Details

### General

|              |  |
|--------------|--|
| Status       | Active   |
| Category     | Circular Industrial Cordsets   |
| Series       | 130006   |
| Description  | Mini-Change A-Size Single-Ended Cordset, 3 Poles, Male (Straight) to Pigtail, 16 AWG, Yellow PVC Cable, 3.66m (12.0') Length |
| IP Rating    | IP67   |
| Product Name | Mini-Change  |
| Type         | Single Ended   |
| UPC          | 78172553226  |

### Agency

|     |         |
|-----|---------|
| CSA | LR6837  |
| UL  | E152210 |

### Electrical

|                               |       |
|-------------------------------|-------|
| Current - Maximum per Contact | 13.0A |
| Voltage - Maximum             | 600V  |

### Physical

|                      |                 |
|----------------------|-----------------|
| Cable Diameter       | 10.41mm (.410") |
| Cable Length         | 3.66m (12.0')   |
| Color - Cable Jacket | Yellow          |
| Connector End A      | Mini-Change     |
| Connector End B      | Pigtail         |

|                               |                         |
|-------------------------------|-------------------------|
| Coupling Style                | Threaded                |
| Gender                        | Male-Pigtail            |
| Keyway                        | Single                  |
| LED Indicator                 | None                    |
| Material - Cable Jacket       | PVC                     |
| Material - Connector Body     | TPE                     |
| Material - Contact            | Brass                   |
| Material - Coupling Nut       | Black Epoxy Coated Zinc |
| Material - Plating Mating     | Gold                    |
| Net Weight                    | 542.496/g               |
| Orientation                   | Straight to Pigtail     |
| Poles                         | 3                       |
| Temperature Range - Operating | -20° to +105°C          |
| Wire/Cable Type               | STOOW                   |
| Wire Size (AWG)               | 16                      |

---

This document was generated on Apr 21, 2026