

Power Matters.™

Home > HS2369A (#18723)

Products

- Product Directory
- Applications Directory
- Parametric Search

HS2369A (#18723)

Overview

Electrical Rating	Symbol	Min	Typ	Max	Unit
DC Current Gain	HFE	40.00		120.00	

Maximum Electrical Rating	Symbol	Min	Typ	Max	Unit
Breakdown Voltage, Collector-Base (Emitter Open)	V _{BR(CBO)}			40.00	V
Collector Current (dc)	I _C			0.20	A
Collector-Emitter Voltage (Base Open)	V _{CEO}			15.00	V
Emitter-Base Voltage (Collector Open)	V _{EBO}			4.50	V
Power Dissipation, Total	P _T			0.36	W

This part can be found in the following product categories:

- Discretes > Transistors > BJT(BiPolar Junction Transistor) > PNP Transistor
- Non-Radiation Hardened Devices > Transistors > BJT(BiPolar Junction Transistor) > NPN Transistor

Related Links

- Technical support
- Sales Contacts
- Available Stock
- Sales Contacts
- RFQ/Samples