



K2C20B1NSP

Active

Photo Not Available



K2C20B1NSP

Cu Mechanical ground conectr to ground 2 Cables to Steel structures, #10-#5 Str., #10-#4 Sol., Connector supplied with Split lock washer and nut

[Image](#) | [Line Art](#) | [3D Model](#) | [Video](#) | [Customer Drawing](#)

[Email Datasheet](#)
[Print Datasheet](#)

Specifications

Dimensional	General	Conductor(s)	Physical	Approvals / Certifications	Other Features
Dimensional					
Stud Length (in)				0.85	
Thread Size				-	
Length (in)				2.06	
Height (in)				1.06	
Nut Width (in)				0.69	
D - in				1.00	
Body Width (in)				0.50	
General					
Product Description				Cu Mechanical ground conectr to ground 2 Cables to Steel structures, #10-#5 Str., #10-#4 Sol., Connector supplied with Split lock washer and nut	
Conductor(s)					
Copper Solid Size (Range)				10-4	
Copper Stranded (Range)				10-5	
Physical					
Type of Plating				Unplated	
Plated (Yes or No)				N	
Product Material				Leaded Bronze Alloy	
Approvals / Certifications					
Rated for Direct Burial				Y	
UL Listed				Y	
CSA Certified				Y	
ROHS Compatible				Exempt	
UL Recognized				N	
CULUS				N	
Industry Standards				UL467	
Other Features					
UPC				7818104677322	