


Chat with a Product Information Specialist



- Connector
- Not Preloaded
- Connector Style = Plug
- Accepts Contact Gender = Receptacle
- Mating Area Interface Dimensions = 6.35 mm

[View all Features](#)

TE Internal Number: 927389-1

✓ Active

 [View 3D PDF](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

- None Available

- None Available

- None Available

- None Available

- None Available

- 2D Drawing (DXF, Version C)
- 3D Model (IGES, Version C)
- 3D Model (STEP, Version C)

- Product Line Information

- Tooling

[List all Documents](#)

- Product Type = Connector
- Mating Area Interface Dimensions (mm [in]) = 6.35 [.250]
- Receptacle Style = Straight
- Color = Black
- Material = Polyamide 6.6
- Keyed = No

- Number of Positions = 3
- Position Keyed = None

- Preloaded = No
- Accepts Contact Gender = Receptacle

- Connector Style = Plug
- UL Flammability Rating = UL 94V-0

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

- Line = Mark I
- Brand = AMP

BOOKMARK

[Careers](#)

[Site Map](#)

[Manage Your Account](#)