
Part Number : 348242245
Product Description : PROPOSED REPLACEMENT: MINI50 GEN II UNSEALED RECEPTACLES (206523 SERIES); Mini50 Unsealed Receptacle, Dual Row, Bridged, with CPA, 24 Circuits, EcoPaXX Resin, Polarization Option B, Gray
Series Number : 34824
Status : Active
Product Category : Connector Housings



Documents and Resources

Drawings

348242245_sd.pdf

PK-31301-538-001.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

AS-34791-020-CH-001.pdf

AS-34791-020-001.pdf

AS-34791-020-CH-001.pdf

AS-34791-020-FR-001.pdf

PS-34791-020-001.pdf

347910020-TS-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Duty-To-Declare
China RoHS	per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21

Downloaded from Arrow.com.

REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	34824
Description	PROPOSED REPLACEMENT: MINI50 GEN II UNSEALED RECEPTACLES (206523 SERIES); Mini50 Unsealed Receptacle, Dual Row, Bridged, with CPA, 24 Circuits, EcoPaXX Resin, Polarization Option B, Gray
Application	Automotive, Power, Wire-to-Board
Product Name	Mini50
UPC	191128232630

Physical

Circuits (maximum)	24
Color - Resin	Gray

Downloaded from Arrow.com.

Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	4.303/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Pitch - Termination Interface	2.00mm
Polarization	B
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mini50 Unsealed Dual Row Vertical Headers	34825
Mini50 Unsealed Dual Row Right-Angle Headers	34826
Mini50 Unsealed Dual Row Right-Angle Headers	34897

Use with Part(s)

Description	Part Number
CTX50 Unsealed Receptacle Terminals	560023

Downloaded from Arrow.com.