Part Number : 643330100
Product Description : CMC Header 112-circuit, 3-pocket, Solder Tail
Series Number : 64333
Status : Active
Product Category : PCB Headers and Receptacles



Documents and Resources

Drawings

643330100_sd.pdf

PK-64333-001-001.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

Specifications

AS-64333-001-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 33
China RoHS	per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS

Downloaded from Arrow.com.

- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	64333
Description	CMC Header 112-circuit, 3-pocket, Solder Tail
Application	Automotive, Power, Wire-to-Board
Comments	Coding: 32w Black, 48w Brown, 32w Grey
Component Type	PCB Header
Product Name	CMC
UPC	883906844455

Electrical

Current - Maximum per Contact	12.0A, 6.0A
Voltage - Maximum	14V DC

Physical

Breakaway	No
Circuits (Loaded)	112
Circuits (maximum)	112
Color - Resin	Black

Downloaded from Arrow.com.

Durability (mating cycles max)	20
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	Yes
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Plating Mating	Tin
Material - Resin	Nylon Alloy
Net Weight	83.100/g
Number of Rows	4
Orientation	Right Angle
Packaging Type	Tray
Pitch - Mating Interface	2.50mm, 3.70mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Solder or Weld

Solder Process Data

Max-Duration	25
Lead-Free Process Capability	WAVE
Max-Cycle	1
Max-Temp	260

Mates With / Use With

Mates with Part(s)

Description	Part Number
.635mm, 1.50mm, CMC Receptacle, 32 Circuits, Left Wire Output, Gray Coding, Mat Sealed	643191218
.635mm, 1.50mm, CMC Receptacle, 32 Circuits, Right Wire Output, Black Coding, Mat Sealed	643193211
.635mm, 1.50mm, CMC Receptacle, 48 Circuits, Right Wire	643203319

Downloaded from Arrow.com.

Output, Brown Coding, Mat Sealed	

Downloaded from Arrow.com.