



Part Number : 734120254

Series Number : 73412

Product Category : RF Cable Assemblies

Product Description : MCRF-to-Pigtail, 1.13mm Cable Diameter, Length 122.00mm, 50 Ohms

Status : Active

Documents & Resources

Drawings
Drawing 734120254_sd.pdf

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	RF Cable Assemblies

Series	73412
Description	MCRF-to-Pigtail, 1.13mm Cable Diameter, Length 122.00mm, 50 Ohms
Assembly Configuration	Single Ended Connector
Connector to Connector	MCRF-to-Pigtail
Product Family	RF Connectors, RF Cable Assemblies and RF Components
Product Name	MCRF
Type	RF Cable Assembly
UPC	822350620291

Electrical

Impedance	50Ω
-----------	-----

Physical

Cable Length	122.00mm
Gender	Plug/Pigtail
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Resin	Polyester
Net Weight	0.400/g
Packaging Type	Bag
Single Ended	Yes
Wire/Cable Type	1.13mm, Coaxial

This document was generated on May 04, 2024