

- [Products](#)

© 2019 TE Connectivity Ltd. family of companies. All Rights Reserved

This product is not currently available. For more information, including distributor inventory, please [contact us](#).

- [Application Tooling](#)
- [Cable Assemblies](#)
- [Portable Crimp Tools](#)

- [Connectors](#)
- [EMI Filters](#)

- [EMI Filters](#)
- [Fiber Optics](#)
- [Fiber Optics](#)

PREM SDE DIE,MINI COAXICON

PREM SDE DIE,MINI COAXICON-91912-3

- [Heat Shrink Tubing](#)
- [Heat Shrink Tubing](#)
- [Identification & Labeling](#)

- [Identification & Labeling](#)
- [Passive Components](#)
- [Passive Components](#)

PREM SDE DIE,MINI COAXICON

- [RMP Systems](#)
- [Power Systems](#)

- TE Internal #: 91912-3
- TE Internal Description: PREM SDE DIE,MINI COAXICON
- [Relays, Contactors & Switches](#)

- **Tool Grade :** *Premium Crimp Tooling*
- [Sensors](#)

- **Die Sets Type :** *Removable/Interchangeable*

- **Specification Type :** *TE Product Specification (114-)*
- [Terminals & Splices](#)

- **Certification :** *Upon Request for Fee*
- [Wire & Cable](#)

SHOP BY BRAND

- **Power Type :** *Battery, Electric, Manual, Pneumatic*
- [Agastat](#)

[See All Features](#)

[More Less](#) [American Sensor Technologies](#)

- [AMP](#)
- [Axicom](#)
- [Buchanan](#)
- **Similar Products**

- [CII](#)
- **Digital Datasheet**
- [DEUTSCH](#)
- [ENERPAC Tooling](#)

- [Hartman](#)
- [HIRSCHMANN MOBILITY](#)

Free Shipping to select countries. Conditions apply. See complete details at [TE Store FAQs](#)

- [Kilovac](#)
- [Medion Optic](#)
- [Measurement Specialties](#)

Get in touch with our product experts.

- [Microdot](#)
- [Potter & Brumfield](#)
- [Raychem](#)

- [Schrack](#)
- **Documents**
- [Industries & Solutions](#)

- [Aerospace](#)
- **Features**

- [Automation & Control](#)
- [Automotive](#)
- [Autosport](#)
- [Communications & Wireless Equipment](#)
- [Connected Home](#)
- [Consumer Solutions](#)
- [Data Centers](#)
- [Defense & Military](#)
- [Energy & Utilities](#)
- [Hybrid & Electric Mobility](#)
- [Industrial Machinery](#)
- [Intelligent Buildings](#)
- [Medical & Healthcare](#)
- [Oil & Gas / Marine](#)
- [Rail](#)
- [Sensor Solutions](#)
- [Truck, Bus & Off-Road Vehicles](#)

Documents

Datasheets & Catalog Pages

- [Coaxial Contacts](#) [ENG_CS_65910_Coaxial_Contacts_0707.pdf](#) English
- [ENG_CS_1-1773865-2_1015.pdf](#) English
- [ENG_DS_1-1773838-7_0718.pdf](#) English
- [ENG_DS_1-1773953-1_0618.pdf](#) English

Instruction Sheets

- [Instruction Sheet \(U.S.\)](#) [ENG_SS_408-8582_A.pdf](#) English

Features

Trends

Please review product documents or [contact us](#) for the latest agency approval information.

- [Internet of Things \(IOT\)](#)
- [Connected Life and Health Tech](#)
- [Electric Vehicles and Connected Transportation](#)
- [Industry 4.0 and Digital Production](#)
- [Smart Connectivity for Smart Cities](#)
- [Partnerships with Inventors and Entrepreneurs](#)
- [Materials Science, 3D Printing, & Digital Manufacturing](#)

Other

- [Tool Grade : *Premium Crimp Tooling*](#)
- [Die Sets Type : *Removable/Interchangeable*](#)
- [Resources](#)
- [Specification Type : *TE Product Specification \(114-\)*](#)
- [Certification : *Upon Request for Fee*](#)
- [Power Type : *Battery, Electric, Manual, Pneumatic*](#)
- [Tool Type : *Standard Die Envelope \(SDE\) Die Set*](#)

[Save preferred products you can export and share](#)

Product Compliance

[Get expert answers fast](#)

EU RoHS Directive 2011/65/EU

- [Product Cross Reference](#)
- [Track Order History](#)
- [Product Compliance](#)
- [Electrical Models](#)
- [Management System Certifications](#)

This declaration covers EU Directive 2011/65/EU incl. Delegated Directive 2015/863/EU. The restrictions under 2015/863/EU apply as of 22 July 2021 for EEE categories 8 (medical devices) and 9 (monitoring and control equipment).

EU ELV Directive 2000/53/EC

[View All Resources](#)

[TE Store](#)

China RoHS 2 Directive MIIT Order No 32, 2016

- [Hi, GivenName](#)
- [Sign Out](#)

EU REACH Regulation (EC) No. 1907/2006

[Product List](#)

- [Current ECHA Candidate List: JUL 2019 \(201\)](#)
- [Candidate List Declared Against: JUN 2016 \(169\)](#)
- [Products](#)
- [Industries & Solutions](#)
- [Resources](#)

Halogen Content

- [TE Store](#)
- [Cart \(0\)](#)
- [Sign Out](#)

Products with Similar Specs

Solder Process Capability

THIS PRODUCT

Products not applicable for solder process capability

Contains Crimp Tools

Industries & Solutions

Statement of Compliance

[Trends](#)

COAXIGON
Compliance Documents

There may be Environmental Compliance related documents on the [DOCUMENTATION Tab](#) [DOCUMENTATION Tab](#)
Our website has detected that you are using an unsupported browser that will prevent you from accessing certain features.

Disclaimer
We strongly recommend that you upgrade to the most recent version of your browser.

Tool Grade : Premium Crimp Tooling
Die Sets Type : Removable/Interchangeable
Specification Type : TE Product Specification (114-)
Certification : Upon Request for...
Due to scheduled maintenance, some services are not functioning on TE.com. We expect everything to be up by 4:30pm EST / 3:30pm CST. Thanks for your patience.
The information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided.
Email or Call Us
Removable/Interchangeable
Specification Type : TE Product Specification (114-)
Certification : Upon Request for...
Welcome to TE's information on RoHS and REACH. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.
14240841

[PREMIUM SDE DIE BNC](#)

In-Stock

- Tool Grade : Premium Crimp Tooling
- Die Sets Type : Removable/Interchangeable
- Specification Type : TE Product Specification (114-)
- Certification : Upon Request for...

Portable Crimp Tools

[91905-1](#)

[PREM SDE DIE, ARINC 3 CRIMP](#)

Non-Stocked

- Tool Grade : Premium Crimp Tooling
- Die Sets Type : Removable/Interchangeable
- Specification Type : TE Product Specification (114-)
- Certification : Upon Request for...

Portable Crimp Tools

[91902-1](#)

[PREM SDE DIE, N SERIES RG 141](#)

In-Stock

- Tool Grade : Premium Crimp Tooling
- Die Sets Type : Removable/Interchangeable
- Specification Type : TE Product Specification (114-)
- Certification : Upon Request for...

[View All Similar Products](#)

These options have been chosen from a pool of Application Tooling with similar specs to this product.

Need help?

Our team is on stand-by and ready to help with your order.

[CHAT NOW](#)

Terms and Conditions

- [I Agree](#)
- [I Disagree](#)

[Call Us](#)

[Live Chat](#)

- [About TE Connectivity](#)
 - [Our Company](#)
 - [Events](#)
 - [TE News Center](#)
 - [Careers](#)
 - [Investors](#)
 - [Corporate Responsibility](#)
- [For Partners](#)
 - [Distributors](#)
 - [Suppliers](#)
- [Support](#)
 - [Customer Service](#)
 - [Find Authorized Distributors](#)
 - [TE Store FAQs](#)
 - [Product FAQs](#)
 - [Terms and Conditions of Sale](#)
- [Call Us](#)
- [Live Chat](#)
- [Contact Us](#)
- **Change Country & Language**

[United States \(EN\)](#)

- Select Country & Language
- [United States \(EN\)](#)
- [Germany \(DE\)](#)
- [China \(中文\)](#)
- [Japan \(日本語\)](#)

Find Your Country/Region

- [Afghanistan \(EN\)](#)
- [Albania \(EN\)](#)
- [Algeria \(EN\)](#)
- [American Samoa \(EN\)](#)
- [Andorra \(EN\)](#)
- [Angola \(EN\)](#)
- [Anguilla \(EN\)](#)
- [Antarctica \(EN\)](#)
- [Antigua and Barbuda \(EN\)](#)
- [Argentina \(EN\)](#)
- [Armenia \(EN\)](#)
- [Aruba \(EN\)](#)

- Australia (EN)
- Austria (EN)
- Azerbaijan (EN)
- Bahamas (EN)
- Bahrain (EN)
- Bangladesh (EN)
- Barbados (EN)
- Belarus (EN)
- Belgium (EN)
- Belize (EN)
- Benin (EN)
- Bermuda (EN)
- Bhutan (EN)
- Bolivia (EN)
- Bonaire (EN)
- Bosnia and Herzegovina (EN)
- Botswana (EN)
- Bouvet Island (EN)
- Brazil (EN)
- British Indian Ocean Territory (EN)
- British Virgin Islands (EN)
- Brunei Darussalam (EN)
- Bulgaria (EN)
- Burkina Faso (EN)
- Burundi (EN)
- Cabo Verde (EN)
- Cambodia (EN)
- Cameroon (EN)
- Canada (EN)
- Cayman Islands (EN)
- Central African Republic (EN)
- Chad (EN)
- Chile (EN)
- China (中文)
- China Hong Kong (EN)
- China Macau (EN)
- China Taiwan (EN)
- Christmas Island (EN)
- Cocos (Keeling) Islands (EN)
- Colombia (EN)
- Comoros (EN)
- Congo (EN)
- Cook Islands (EN)
- Costa Rica (EN)
- Croatia (EN)
- Curaçao (EN)
- Cyprus (EN)
- Czech Republic (EN)
- Côte d'Ivoire (EN)
- Democratic Republic of the Congo (EN)
- Denmark (EN)
- Djibouti (EN)
- Dominica (EN)
- Dominican Republic (EN)
- Ecuador (EN)
- Egypt (EN)
- El Salvador (EN)
- Equatorial Guinea (EN)
- Eritrea (EN)
- Estonia (EN)
- Ethiopia (EN)
- Falkland Islands (EN)
- Faroe Islands (EN)
- Fiji (EN)
- Finland (EN)
- France (EN)
- French Guiana (EN)
- French Polynesia (EN)
- French Southern Territories (EN)
- Gabon (EN)
- Gambia (EN)
- Georgia (EN)

- Germany (DE)
- Ghana (EN)
- Gibraltar (EN)
- Greece (EN)
- Greenland (EN)
- Grenada (EN)
- Guadeloupe (EN)
- Guam (EN)
- Guatemala (EN)
- Guernsey (EN)
- Guinea (EN)
- Guinea-Bissau (EN)
- Guyana (EN)
- Haiti (EN)
- Heard Island and McDonald Islands (EN)
- Honduras (EN)
- Hungary (EN)
- Iceland (EN)
- India (EN)
- Indonesia (EN)
- Iraq (EN)
- Ireland (EN)
- Isle of Man (EN)
- Israel (EN)
- Italy (EN)
- Jamaica (EN)
- Japan (日本語)
- Jersey (EN)
- Jordan (EN)
- Kazakhstan (EN)
- Kenya (EN)
- Kiribati (EN)
- Kuwait (EN)
- Kyrgyzstan (EN)
- Laos (EN)
- Latvia (EN)
- Lebanon (EN)
- Lesotho (EN)
- Liberia (EN)
- Libya (EN)
- Liechtenstein (EN)
- Lithuania (EN)
- Luxembourg (EN)
- Macedonia (EN)
- Madagascar (EN)
- Malawi (EN)
- Malaysia (EN)
- Maldives (EN)
- Mali (EN)
- Malta (EN)
- Marshall Islands (EN)
- Martinique (EN)
- Mauritania (EN)
- Mauritius (EN)
- Mayotte (EN)
- Mexico (EN)
- Micronesia (EN)
- Moldova (EN)
- Monaco (EN)
- Mongolia (EN)
- Montenegro (EN)
- Montserrat (EN)
- Morocco (EN)
- Mozambique (EN)
- Myanmar (EN)
- Namibia (EN)
- Nauru (EN)
- Nepal (EN)
- Netherlands (EN)
- New Caledonia (EN)
- New Zealand (EN)
- Nicaragua (EN)

- Niger (EN)
- Nigeria (EN)
- Niue (EN)
- Norfolk Island (EN)
- Northern Mariana Islands (EN)
- Norway (EN)
- Oman (EN)
- Pakistan (EN)
- Palau (EN)
- Palestine (EN)
- Panama (EN)
- Papua New Guinea (EN)
- Paraguay (EN)
- Peru (EN)
- Philippines (EN)
- Pitcairn (EN)
- Poland (EN)
- Portugal (EN)
- Puerto Rico (EN)
- Qatar (EN)
- Romania (EN)
- Russia (EN)
- Rwanda (EN)
- Réunion (EN)
- Saint Barthélemy (EN)
- Saint Helena, Ascension and Tristan da Cunha (EN)
- Saint Kitts and Nevis (EN)
- Saint Lucia (EN)
- Saint Martin (EN)
- Saint Pierre and Miquelon (EN)
- Saint Vincent and the Grenadines (EN)
- Samoa (EN)
- San Marino (EN)
- Sao Tome and Principe (EN)
- Saudi Arabia (EN)
- Senegal (EN)
- Serbia (EN)
- Seychelles (EN)
- Sierra Leone (EN)
- Singapore (EN)
- Sint Maarten (EN)
- Slovakia (EN)
- Slovenia (EN)
- Solomon Islands (EN)
- Somalia (EN)
- South Africa (EN)
- South Georgia and the South Sandwich Islands (EN)
- South Korea (EN)
- Spain (EN)
- Sri Lanka (EN)
- Suriname (EN)
- Svalbard and Jan Mayen (EN)
- Swaziland (EN)
- Sweden (EN)
- Switzerland (EN)
- Tajikistan (EN)
- Tanzania (EN)
- Thailand (EN)
- Timor-Leste (EN)
- Togo (EN)
- Tokelau (EN)
- Tonga (EN)
- Trinidad and Tobago (EN)
- Tunisia (EN)
- Turkey (EN)
- Turkmenistan (EN)
- Turks and Caicos Islands (EN)
- Tuvalu (EN)
- U.S. Virgin Islands (EN)
- Uganda (EN)
- Ukraine (EN)
- United Arab Emirates (EN)

- United Kingdom (EN)
- United States (EN)
- United States Minor Outlying Islands (EN)
- Uruguay (EN)
- Uzbekistan (EN)
- Vanuatu (EN)
- Vatican City (EN)
- Venezuela (EN)
- Vietnam (EN)
- Wallis and Futuna (EN)
- Western Sahara (EN)
- Yemen (EN)
- Zambia (EN)
- Zimbabwe (EN)
- Åland Islands (EN)

- [Terms of Use](#)
- [Privacy](#)
- [Cookie Policy](#)
- [Accessibility](#)
- [Site Map](#)

• © 2019 TE Connectivity. All Rights Reserved.

- [Facebook](#)
- [Twitter](#)
- [LinkedIn](#)
- [YouTube](#)
- [Instagram](#)

- [Facebook](#)
- [Twitter](#)
- [LinkedIn](#)
- [YouTube](#)
- [Instagram](#)

© 2019 TE Connectivity. All Rights Reserved.

View this page on [TE mobile site](#).